

# LUVOCOM 3F PA<sup>HT</sup>® CF 9743 BK

High-temperature polyamide  
with carbon fibers, black

Physical properties		Test method	Specimen	Units	Typical value
Specific gravity		ISO 1183-3		g/cm <sup>3</sup>	1,29
Water absorption	23°C / 24h	ISO 62	ISO 3167 A	%	<0,3
Melt flow rates (MFR)		250°C / 2,16kg	pellet	g/10 min	8
Melt volume rate (MVR)		250°C / 2,16kg	pellet	cm <sup>3</sup> /10 min	6
Linear mould shrinkage		DIN 16742	ISO 3167 A	%	0,3-0,5

Mechanical properties at 23°C / 50% rh					
Tensile strength	dry, @50 mm/min	ISO 527	ISO 3167 A	MPa	250
Elongation @Fmax.	dry, @50 mm/min	ISO 527	ISO 3167 A	%	1,4
Tensile modulus	dry, @1 mm/min	ISO 527	ISO 3167 A	GPa	28
Impact strength	dry	ISO 179 1eU	80x10x4mm	kJ/m <sup>2</sup>	55

Thermal properties					
Heat distortion temp.	HDT A	ISO 75	80x10x4mm	°C	240
Continuous service temp.	20.000 h	IEC 60216	ISO 3167 A	°C	150
Service temperature	during lifetime max. 200h		ISO 3167 A	°C	180

Electrical properties					
Insulation resistance	strip electrode R25	DIN EN 62631-3-3	ISO 3167 A	Ω	≤10 <sup>2</sup>
Surface resistance	ROB	DIN EN 62631-3-2	Ronde 60x4mm	Ω	<10 <sup>2</sup>

## Main features

Low influence from moisture and temperature on dimensional stability and electrical properties, compared with PA66

# LUVOCOM 3F PA<sup>HT</sup>® CF 9743 BK

High-temperature polyamide  
with carbon fibers, black

## Recommended processing parameters

### General

3D Printing parameters may vary from machine to machine. The following settings may be used as an indication: nozzle temperature: 265 - 290 °C / nozzle material: abrasion resistant / print bed temperature: > 50 °C / layer thickness: > 0,2mm / printing speed 40 - 60 mm/s.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

### Delivery form & storage

Unless indicated otherwise, the material is delivered as 3mm long pellets in sealed bags on pallets. Preferably storage should be effected in dry and normally temperatured rooms.

### Predrying

It is advisable to predry the granules with a suitable dryer immediately before processing. The granule may absorb moisture from the environment.

Dryer type	Temperature °C	Drying time in h
Dehumidifying dryer	130	6 - 8
Vacuum Dryer	120	4 - 6

### Recommended processing parameters

In general LUVOCOM® 3F can be processed on conventional extrusion machines while observing the usual technical guidelines. Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder, screw and die should be protected against wear as is usual in the processing of reinforced thermoplastic materials. Lengthy dwell times for the melts in the cylinder should be avoided. Lower the temperatures during interruptions!

Nozzle	Zone 3	Zone 2	Zone 1
250 - 290 °C	260 - 300 °C	260 - 300 °C	260 - 300 °C

### Additional information

Filaments produced from this material may be wound into standard size spools.

09743 21 06 18

#### Europe and Head Office

Lehmann&Voss&Co. KG  
Alsterufer 19  
20354 Hamburg  
Germany  
Tel +49 40 44 197-0  
Email: [luvocom@ehvoss.de](mailto:luvocom@ehvoss.de)

#### North America

LEHVOSS North America, LLC  
185 South Broad Street  
Pawcatuck, CT 06379  
USA  
Tel +1-855-681-3226  
Email: [info@ehvoss.us](mailto:info@ehvoss.us)

#### Asia

LEHVOSS (Shanghai) Chemical Trading Co., Ltd.  
Unit 4805, 8 Xingyi Road  
Changning District, Shanghai 200336  
China  
Tel +86 21 62785181  
Email: [info@ehvoss.cn](mailto:info@ehvoss.cn)

